

Rapid Work light The Portable

The rechargeable LED work light The Portable is the optimal work lighting in the garage, shed, in the attic or when working outdoors where you do not have power. The Portable has a bright light of 1000 lumens with good dispersion, featuring two lighting modes (100% and 50%), and is easy to carry. The IP65 rating means that it is fully dustproof and protected against water spray from all directions, so that The Portable can be used outdoors even in the rain. Integrated USB-C charged battery, with a runtime of about 3 hours; charging cable included. The work light's stable stand can be tilted for different light dispersions. The Portable also has a USB-A port if you need to use the light as a power bank for your discharged mobile phone, for example.



Attributes

- Perfect working light when you don't have a power socket
- Bright light with good dispersion (1000 lumens)
- Two lighting modes (100% / 50%)
- Runtime of about 3 hours
- Fully dustproof and protected against water spray from all directions (IP65)
- Easy and comfortable to carry
- 180° tiltable head
- Can also be used as a power bank
- Integrated Li-ion battery – charging time approx 4 h
- USB-C cable for charging included

Specifications

Number	5001731
Colour	-----
Dimensions (W x H x D)	175 x 130 x 45 mm
Weight	530 g
Pallet quantity	384
EAN code	4051661044205