



## BRONZE GLOBE VALVE GV32B

## DESCRIPTION

GV32B bronze in line stop valves, screwed type for use on steam, water, oil or air applications.

## MAIN

FEATURES :	Rising stem PTFE renewable disk High quality PTFE packing			

USE: Saturated steam, condensate, water, oil, compressed air and other fluids compatible with the construction.

MODELS: GV32B

SIZES : DN1/2" - 2"

CONNECTIONS: Female screwed ISO7/1Rp(BS21)

## LIMITING

CONDITIONS : Body design conditions: PN32 198°C at 14 bar 100°C at 32 bar


FLOW RATE COEFFICIENTS						
	SIZES					
	1/2"	3/4"	1"	11/4"	11/2"	2"
Kvs	2	5	10	16	23	42

Kvs in m3/h , see data sheet IS PV10.00 E ; For conversion Kvs =  $Cv(US) \times 0.855$ 

	DIMENSIONS				
DN	A (mm)	B (mm)	C (mm)	Weight (Kgs)	
1/2"	57	95	75	0,39	
3/4"	65	98	75	0,55	
1"	78	114	85	0,85	
11/4"	89	138	95	1,36	
11/2"	100	159	105	1,76	
2"	121	170	120	2,62	

MATERIALS				
POS.	DESIGNATION	MATERIAL		
1	Valve Body	Bronze		
2	Bonnet	Forged brass		
3	Stem	Brass		
4	Disk	Glass filled PTFE		
5	Disk nut	Brass		
6	Packing	PTFE		
7	Handwheel	Aluminium		





CE MARKING (PED-European Directive 97/23/EC)			
PN 32	Category		
DN 1/2" to 11/4"	SEP-art.3, paragraph 3		
DN 11/2" and DN 2"	Cat. 1 (CE Marked)		

We reserve the right to change the design and material of this product without notice.