

DCS386T1-GB

18V XR Reciprocating Saw With FLEXVOLT ADVANTAGE - 1 X 6Ah

Take advantage of more power using 18V XR tools with FLEXVOLT ADVANTAGE technology. A unique electronic module with pack identification technology enables the tool to recognise when an XR FLEXVOLT battery is attached and unlock even more power. The DCS386 delivers up to 50% more power when paired with a DCB546 XR FLEXVOLT 6Ah battery versus a DCB184 18V XR 5Ah battery. The DCS386 has been equipped with a crank type drive train for smoother, more efficient operation and reduced vibration, and delivers an impressive no-load speed of 3,000spm.



Selling Propositions

- DEWALT Brushless Motor for extended run-time, reliability & durability
- Intelligent variable speed trigger and lock off switch
- Lever action keyless blade clamp for tool-free blade change
- Pivoting Shoe with open top for high stability and visibility during a cut
- LED for clear illumination
- Ergonomiška, guma padengta, rankena užtikrina neprilygstamą naudotojų komfortą

Standard Equipment

- TSTAK-tööriistakast (1)
- 54V XR Flexvolt Li-Ion battery pack with state of charge indicator (1)
- Multi Voltage Charger (1)

Warranty specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
No Load Stroke Rate	0-3000 spm
Max. Cutting Capacity (Wood)	300.0 mm
Max. Cutting Capacity (Steel Section and Pipes)	130.0 mm
Max. Cutting Capacity [PVC]	160.0 mm
Weight	3.5 kg
Battery Capacity	6.0 Ah
Length	440.0 mm
Height	160.0 mm
Sound Pressure	84.0 dB(A)
Sound Pressure Uncertainty	5.0 dB(A)
Sound Power	95.0 dB(A)
Sound Power Uncertainty	5.0 dB(A)
Hand/Arm Vibration - Cutting boards	18.0 m/s ²
Uncertainty K 2 (Vibration)	4.2 m/s ²
Hand/Arm Vibration - Cutting wooden beams	15.0 m/s ²
Uncertainty K 3 (Vibration)	1.5 m/s ²