


# PRODUCT SPECIFICATION

<b>Brand</b>	C.K
<b>Product Range</b>	ST tape measures
<b>Catalogue number</b>	3442
<b>Date</b>	07/05/2013

<p><b>Range Description</b> A range of three sizes of professional specification tape measures.</p>				
<p><b>Features</b></p> <p>The ST range from C.K features:</p> <ul style="list-style-type: none"> <li>• 73/362/EEC Class II accuracy - for confident results.</li> <li>• ABS plastic housing - tough for damage protection with a soft feel for comfort</li> <li>• Lock and pause buttons - for control and convenience</li> <li>• A recoil damper - to prevent damage to the tape and hook on recoil. on 5m/16" and 7.5m/25' sizes</li> <li>• Sprung belt hook for convenient carrying</li> <li>• Nylon coated blade for abrasion resistance</li> <li>• 16" Joist center markings</li> <li>• True zero hook</li> </ul> <p>The ST range is available in 3m/10' and 5m/16' and 7.5m/25' sizes.</p>				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3442 10	ST tape 3m/10ft Metric and Imperial markings	5013969959604	90178010	6
T3442 16	ST tape 5m/16ft Metric and Imperial markings	5013969959611	90178010	6
T3442 25	ST tape 8m/25ft Metric and Imperial markings	5013969959628	90178010	6
T3442M3	ST tape 3m Metric markings	5013969959635	90178010	6
T3442M5	ST tape 5m Metric markings	5013969959642	90178010	6
T3442M8	ST tape 8m Metric markings	5013969959659	90178010	6

Technical product information	Blade widths 3m/10' – 13mm 5m/16' – 19mm 7.5m/25' – 25mm
Standards compliance	The graduations printed on the tape blade conform to the accuracy requirements of 73/362/EEC Class II  
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K products are guaranteed for life against imperfect materials or workmanship Tape measures contain moving parts that may wear over time, these are not covered under the terms of the warranty
Country of origin	Taiwan

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3442 10	68	25	57	78	125	50	155	106
T3442 16	75	35	64	176	125	50	155	204
T3442 25	88	40	75	348	125	50	155	376
T3442M 3	68	25	57	78	125	50	155	106
T3442M 5	75	35	64	176	125	50	155	204
T3442M 8	88	40	75	348	125	50	155	376

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3442 10	135	325	170	816		
T3442 16	135	325	170	1404		
T3442 25	135	325	170	2436		
T3442M 3	135	325	170	816		
T3442M 5	135	325	170	1404		
T3442M 8	135	325	170	2436		

### Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3442 10	22	Blister	6	Card			180	Box
T3442 16	22	Blister	6	Card			180	Box
T3442 25	22	Blister	6	Card			180	Box
T3442M 3	22	Blister	6	Card			180	Box
T3442M 5	22	Blister	6	Card			180	Box
T3442M 8	22	Blister	6	Card			180	Box