

FEATURES

- 300mm / 12 in dual scales
- Hardened stainless steel body with satin chrome plated finish
- Four-way measurement for Outside, Inside, Depth and Step
- Scale graduations: 0.001" and 0.02mm

RS PRO 600mm Vernier Caliper, Metric & Imperial

RS Stock No.: 136-8086



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO fine adjustment Vernier Calipers feature dual scales with both metric and imperial readings of internal and external precision measurements. The adjustable mechanism has two lock screws so you can accurately measure objects with ease. The calipers sliding surfaces are raised to prevent wear to the scale. Internal jaws, external jaws and a sliding depth rod provide four ways to measure.

General Specifications

Caliper Type	Vernier
Imperial or Metric	Both
Display Type	Analogue
Accuracy	+/-0.04mm
Thumb roller	No
Data Output	No
Applications	For use in laboratories, electrical and electronic servicing, and maintenance, mechanical and automotive applications

Mechanical Specifications

Capacity	600mm
External Jaw Length	600mm/24
Internal Jaw Length	0.001in
Internal Min. Diameter	0.001 in
Inch Grads	0.001 in
Metric Grads	0.02mm
Accuracy External Jaws	±0.04mm
Accuracy Internal Jaws & Depth Rod	±0.08mm

