



PRODUCT-DETAILS

TYG34M

CABLE TIE 40LB 6IN NAT NYL BLIND MT



General Information

Extended Product Type	TYG34M
Product ID	7TCG009520R0078
EAN	5414363067320
Catalog Description	CABLE TIE 40LB 6IN NAT NYL BLIND MT
Long Description	Blind Mounting Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 160mm (6.3 Inches), Width of 3.6mm (0.142 Inches), Thickness of 1.1mm (0.043 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), Bulk Pack

Ordering

EAN	5414363067320
UPC	786210519647

Dimensions

Product Net Width	0.142 in 3.6 mm
Product Net Depth / Length	6.3 in 160 mm

Container Information

Package Level 1 Units	1000 piece
-----------------------	------------

Package Level 2 Units	10000 piece
Package Level 2 Width	10.2 in 259 mm
Package Level 2 Height	13.8 in 351 mm
Package Level 2 Depth / Length	19.7 in 500 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19980621
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	TY-RAP FASTENING
Product Type	Blind Mounting
Tensile Strength	40 lb 180 N
Thickness	0.043 in 1.1 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TYG34M
Instructions and Manuals	TYG34M

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

