



54V XR FLEXVOLT 190mm Circular Saw – 2 X 6Ah

DCS578T2-QW

54V FLEXVOLT system giving corded performance
DEWALT Brushless Motor for power, extended run-time, reliability & durability

General purpose ripping, crosscutting and bevelling circular saw for wood and other construction materials

Variable adjustment of the bevel angle to 57 degrees

Scale for precise cutting depth setting to 67 mm



Sound Pressure Uncertainty	3 dB(A)
----------------------------	---------

Sound Pressure	90 dB(A)
----------------	----------

Uncertainty K 1 (Vibration)	1.5 m/s ²
-----------------------------	----------------------

Battery Capacity	6 Ah
------------------	------

Power Source	Cordless
--------------	----------

No Load Speed	5800 Rpm
---------------	----------