

Part Number: 0982660117
Status: Active
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 30.00mm Cable Length, Tin (Sn) Plating, 12 Circuits

Documents:
図面 (PDF) Datasheet (PDF)
製品仕様書 PS-98266-001-001 (PDF) RoHS Certificate of Compliance (PDF)

一般 コメント Crimp Quality Equipment 概要	Contacts on the same side, Type A Yes FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
製品名 UPC	Premo-Flex FFC Jumper 756054767504
機械的性能/材質 ケーブル長 極数 (実装) Contact Layout Type 材質 - 嵌合部メッキ Net Weight 梱包形態 ピッチ - 嵌合部 (インチ) 使用温度範囲 電線サイズ (AWG) ケーブル種別	30.00mm 12 A (same side) 錫 0.134/g ポリ袋 0.50mm -40° to +105° C N/A FFC
電気的性能 最大定格電流 最大定格電圧	0.5A 60V AC
参考情報	
図面・仕様書情報 製品仕様書 製品図面	PS-98266-001-001 SD-98266-001-001



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per -ECHA_01_2020 (16 January 2020 Halogen-Free Status Not Low-Halogen	China RoHS
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Contained

Search Parts in this Series
98266 Series

Mates With
Easy-On FFC/FPC Connector:

527451233 , 527461233 , 525591233