

## FEATURES

- **UV Resistant:** Ensures longevity and reliability in outdoor applications.
- **High Tensile Strength:** Withstands up to 8 kg, providing secure fastening.
- **Nylon Material:** Offers durability and resistance to wear and tear.
- **Compact Size:** 100 mm length and 2.5 mm width for versatile use.
- **RoHS Compliant:** Meets safety and environmental standards.

## RS PRO UV Protected Cable Tie, 100 mm Nylon

RS Stock No: 656-025



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

These RS PRO UV Protected Cable Ties are designed for securing and organising cables in both indoor and outdoor environments. Made from durable nylon, they offer excellent resistance to UV radiation, making them ideal for use in harsh weather conditions. With a maximum bundle diameter of 22 mm, they provide a reliable solution for managing cable installations efficiently.

### General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	UV Protected Cable Tie
Tensile Strength	8 kg

### Protection Category

Fire Behaviour	UL 94HB
UV Resistant	Yes

### Mechanical Specifications

Length	100 mm
Material	Nylon
Maximum Bundle Diameter	22 mm
Width	2.5 mm

### Approvals

Standards/Approvals	RoHS, UL94HB
---------------------	--------------