

0 601 9J9 070 – GSB 12V-35

Material number	0 601 9J9 070
EAN	4059952513997
1 x belt clip, 1 x bit holder	✓
1/2 L-BOXX inlay for accessories 1 600 A00 2WY	✓
1/2 L-BOXX inlay for tool and charger 1 600 A00 2V2	✓
2 x battery GBA 12V 3.0Ah 1 600 A00 X79	✓
L-BOXX 102 1 600 A01 2FZ	✓
Quick charger GAL 12V-40 Professional 1 600 A01 9R4	✓



Technical data

Technical data

Torque (soft/hard/max.)	20/35/- Nm
No-load speed (1st gear / 2nd gear)	0 – 460 / 0 – 1,750 rpm
Battery type	Lithium-ion
Max. impact rate	26.250 bpm
Chuck capacity, min./max.	0.8 / 10 mm
Weight excl. battery	0.8 kg
Torque settings	20+1
Tool dimensions (height)	160 mm
Packaging dimensions (width x length x height)	357 x 442 x 117 mm
Clamping range, min.	0,8 mm
Clamping range, max.	10,0 mm
Battery capacity	3,0 Ah
Battery voltage	12 V
Charging time (80%/100%) approx.	36/50 min [3.0 Ah]
Weight incl. battery	1,0 kg
Noise level	The A-rated noise level of the power tool is typically as follows: Sound pressure level dB(A); Sound power level dB (A). Uncertainty K= dB.

Drilling diameter

Max. drilling diameter in wood	32 mm
Max. drilling diameter in steel	10 mm
Max. drilling diameter in masonry	10 mm

Screw diameter

Max. screw diameter	8 mm
---------------------	------

Noise/vibration information

Sound pressure level	87 dB(A)
Sound power level	98 dB(A)
Uncertainty K	5 dB



Sales information

Positioning

- Perfect balance between compactness, productivity and performance

User benefit

- Highest impact rate in the 12V category, enabling powerful impact drilling of up to Ø10 mm in masonry
- Compact design allows perfect handling and easy operation – even in challenging working situations
- High rotation speed of 1,750 rpm for a broad variety of jobs