

# ELECTRONIC-SERVICE TOOL SETS



the tool sets for mobile use at electrostatically endangered components



Outside dimensions: 320 x 250 x 50 mm (closed)

## 2220 BERNSTEIN® Service-Set Antistatic

Elegant zipper case, made from dissipative black imitation leather and dissipative pockets for 12 ESD-tools and foldable ESD-workbench pad with accessories. **Weight with tools:** 0.950 kg

No.	Description of individual tools	No.	Description of individual tools
2-620	PLCC-extractor	4-621	Cross-recess screwdriver size 000, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip
3-601-13	Side cutters, 120 mm, semi flush, for soft wire up to 1.5 mm Ø and hard wire up to 0.4 mm Ø, bright steel-polished, box joint, double leaf spring, with dissipative black hand guard	4-622	Cross-recess screwdriver size 00, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip
3-632-13	Flat nose pliers, 120 mm, plain jaws, bright steel-polished, box joint, double leaf spring, with dissipative black hand guard	4-623	Cross-recess screwdriver size 0, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip
3-633-13	Snipe nose pliers, 120 mm, plain jaws, bright steel-polished, box joint, double leaf spring, with dissipative black hand guard	5-191	Tweezers, made from conductive plastic material, reinforced with glass fibre, 120 mm, with straight, rounded tips
4-601	Slotted screwdriver with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip, 50 x 0.8 mm	5-192	Tweezers, made from conductive plastic material, reinforced with glass fibre, 120 mm, with straight, 3 mm flat-hand tips
4-605	Slotted screwdriver with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip, 60 x 2.0 mm	9-354	ESD-handling-set, consisting of: foldable green workbench pad (surface resistance according to DIN 53482: approx. 10 <sup>9</sup> ohm), 500 x 400 x 0.35 mm, contact bracelet 9-342, earth wire 2500 mm long with 1 Mohm safety resistor
4-606	Slotted screwdriver with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip, 60 x 2.5 mm		