



Main

Range	Unica
Product or component type	Connector
Accessory / separate part category	Cable accessories
Poles description	1P + N + E
Quantity per set	5

Complementary

Mounting mode	By screws
Connection position	Direct connection
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Electrical circuit type	Power supply
Electrical connection	Cable 1.5...2.5 mm ² - rigid or stranded
Cable outer diameter	9 mm
Height	32 mm
Width	24 mm
Depth	35 mm
Material	PA (polyamide) PC (polycarbonate)
Colour	White
Product compatibility	Power distribution module

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information