

160 i/165 i/7 Rack screwdriver set Kraftform Plus Series 100, voltage tester and rack, 7 pieces  
Kraftform Plus – Series 100 VDE



<b>EAN:</b>	4013288041715	<b>Size:</b>	280x205x55 mm
<b>Part number:</b>	05006148001	<b>Weight:</b>	666 g
<b>Article number:</b>	160 i/165 i/7 Rack	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Insulated VDE blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Lasertip tips for more secure fit in the screw head

7-piece screwdriver set with individually tested, insulated screwdrivers as per IEC 60900. Individual testing in a water bath at 10,000 volts so as to ensure safe working at the permitted voltage of 1,000 volts. Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Partially Lasertip: the tip literally bites itself into the screw head and prevents any slipping. "Take it easy" Tool Finder: colour coding according to profile and size. The anti-roll feature prevents any bothersome rolling away at the workplace. Including voltage tester and 1 rack for storage.

**Web link**

[https://products.wera.de/en/vde\\_tools\\_kraftform\\_plus\\_series\\_100\\_vde\\_160\\_i\\_165\\_i\\_7\\_rack.html](https://products.wera.de/en/vde_tools_kraftform_plus_series_100_vde_160_i_165_i_7_rack.html)

Wera - 160 i/165 i/7 Rack  
05006148001 - 4013288041715

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**160 i/165 i/7 Rack screwdriver set Kraftform Plus Series 100, voltage tester and rack, 7 pieces**  
**Kraftform Plus – Series 100 VDE**



**Set contents:**



**165 i PZ VDE**

05006162001 1 x PZ 1 x 80 mm  
 05006164001 1 x PZ 2 x 100 mm



**160 i VDE**

05006100001<sup>1)</sup> 1 x 0,4 x 2,5 x 80 mm  
 05006110001 1 x 0,6 x 3,5 x 100 mm  
 05006115001 1 x 0,8 x 4 x 100 mm  
 05006120001 1 x 1 x 5,5 x 125 mm  
 05006120001 1 x 1 x 5,5 x 125 mm



<sup>1)</sup> without Lasertip



**247**

05005655001<sup>1)</sup> 1 x 0,5 x 3 x 70 mm




<sup>1)</sup> Product not available in the USA and Canada.

**Individually tested**



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

**Impact strength test**



Impact strength tested at  $-40^{\circ}\text{C}$ , guaranteeing safety even under extreme conditions.

**Lasertip**



A precisely-focused laser creates a sharp-edged surface structure. This laser treatment results in an edge hardness of up to 1000 HV 0.3. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

**Web link**

[https://products.wera.de/en/vde\\_tools\\_kraftform\\_plus\\_series\\_100\\_vde\\_160\\_i\\_165\\_i\\_7\\_rack.html](https://products.wera.de/en/vde_tools_kraftform_plus_series_100_vde_160_i_165_i_7_rack.html)

Wera - 160 i/165 i/7 Rack  
 05006148001 - 4013288041715

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de

Reduced contact pressure



Wera Lasertip reduces the contact pressure required and enhances force transfer – meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

Kraftform




The basic idea for the prototype of the Kraftform handle – that the hand should dictate the design – has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

Non-roll feature



All Kraftform screwdrivers have a non-roll feature at the lower end of the handle. The hexagonal design prevents any annoying rolling away of the screwdriver at the workplace.

“Take it easy” Tool Finder



Screwdrivers with “Take it easy” tool finder: colour coding according to profile and size stamp.

Web link

[https://products.wera.de/en/vde\\_tools\\_kraftform\\_plus\\_series\\_100\\_vde\\_160\\_i\\_165\\_i\\_7\\_rack.html](https://products.wera.de/en/vde_tools_kraftform_plus_series_100_vde_160_i_165_i_7_rack.html)

Wera - 160 i/165 i/7 Rack  
 05006148001 - 4013288041715

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de