

FR75 - Hi-Vis FR Vest

Collection: Bizflame™ Vest HV

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Vest HV: 100% Polyester, Warp Knitted

Outer Carton: 60

Product information

The FR75 is a great addition to our Flame Retardant vest collection. Certified to EN ISO 20471 Class 2 and EN ISO 14116 Index 1, the vest must be worn over Index 2 or 3 garments to offer flame retardant protection.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.



Standards

EN ISO 14116 Index 1

EN ISO 20471 Class 2

RIS 3279 TOM Issue 2 (Orange Only)

Features

- Premium sew on flame resistant reflective tape
- Hook and loop closure for easy access
- Non-magnetic - nickel and ferrous free
- Lightweight and comfortable
- Generous fit for wearer comfort
- CE certified
- UKCA marked
- Complies with RIS 3279-TOM for rail industry (orange only)

FR75 - Hi-Vis FR Vest

Commodity Code: 6110309100

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/14704-01/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
 SATRA Technology Park
 NN16 8SD, United Kingdom
 Cert No: AB0321/16512-01/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
FR75YERS/M	Yellow	43.0	28.0	55.0	0.2420	0.0662	5036108204540	15036108693075
FR75YERL/XL	Yellow	43.0	28.0	55.0	0.2600	0.0662	5036108204533	15036108693068
FR75YERXX/3X	Yellow	43.0	28.0	55.0	0.2840	0.0662	5036108204557	15036108693082
FR75YER4X/5X	Yellow	43.0	28.0	55.0	0.3450	0.0662	5036108266654	15036108756411