

Datasheet

RS Pro Feed Through Terminal Block, CTS series, 1000 V, 24A, Screw Clamp Termination, Blue, Single Level

RS Stock No: **796-1031**



Product Details

RS Pro feed through terminal block in blue colour, has 1000 V voltage rating and 24 A current rating. This single level, screw clamp termination system has marker holding recesses to accept marking tags for circuit identification. This block makes cross connection easy with the aid of shorting links/sleeves and screws. It is suitable for control, automation, instrumentation and power distribution applications.

Features and Benefits

- Rated voltage 1000 V
- Marker holding recesses to accept marking tags for circuit identification
- Wire entry orientation side entry
- Suitable for control, automation, instrumentation and power distribution applications

**Specifications:**

Colour	Blue
Current Rating	24 A
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C
Number of Levels	Single
Termination Method	Screw Clamp
Voltage Rating	1000 V
Wire Size	22 to 12 AWG
Dimensions	43 x 5 mm
Material	Polyamide Housing
Screw Size	M2.5
Standards Met	CE, CSA US, IEC