

issuDOM - TP100

Touch-bars - 1 point



Technical features

Type of mounting	Rim lock
Number of locking points	1
Application	Aluminium, steel, wooden doors, PVC profiles, emergency exit doors, doors for heavy traffic areas
Reversible	Yes
Fire resistant	Yes
Outside opening	Knob or handle
Bar dimension	840 mm
Bar finish	Lacquered
Material of the cases	Steel/zamak
Protection	Anti-corrosion treatment
Certifications and Standards	Certified EN 1125: 2008 Level 7 (max.) Certifire Certification
Durability test	More than 200 000 cycles opening/closing
Supplied accessories	Strike plate, screws, cover plate
On request	1170 and 1300 mm bar dimensions



Logistics



≈ 3,000 kg



Individual box



Design
Fire resistant as standard
Reversible without disassembling
Easy adjustment of length by cutting

Additional products



Exit pad



Exterior accessories with knob or handle



Adaptation kit

issuDOM - TP100

Touch-bars - 1 point



BAR DIMENSION	FINISH	ARTICLE NUMBER
840	White RAL 9016	F2PU1PT0001
840	Aluminium tone RAL 9006	F2PU1PT0002
840	Black RAL 9005	F2PU1PT0003
Dimensions in mm		

