



PRODUCT-DETAILS

SSAMHL32/25M

32MM STST CORE ANTI MICRO COND 25M



概要信息	
产品型号	SSAMHL32/25M
产品ID	7TCA296030R0516
欧洲商品编号(EAN)	5020963807381
目录说明	32MM STST CORE ANTI MICRO COND 25M
详细描述	Liquidtight. Anti-Microbial Conduit, Conduit Size - Metric 32 Millimeters / US Trade Size 1 Inch, Outside Diameter 33.1mm, Inside Diameter 26.7mm, Static Bend Radius 144mm, IP40-IP69 Rating, Stainless Steel String Packed with Thermoplastic Jacket, Reel Length 25 Meters, White

其他信息	
应用	Suitable for indoor splash zone areas or food processing equipment
产品应用类型	Anti-Microbial Conduit

订货信息	
欧洲商品编号(EAN)	5020963807381
UPC	786210159768

尺寸	
产品净深	25 m

技术参数	
Number of Batteries	0
颜色	White
材料	Galvanised Steel Core, String Packed and Thermoplastic Jacket

环境条件	
WEEE 类别	Product Not in WEEE Scope

包装信息	
1级包装单元	1 piece
1级包装高度	10.62 in 270 mm
1级包装长度	26.77 in 680 mm
1级包装宽度	26.77 in 680 mm

认证及声明（文件编码）	
数据手册，技术资料	SSAMHL32/25M
说明书和手册	SSAMHL32/25M
符合性声明 - CE	9AKK107492A9618
RoHS信息	9AKK107992A8994
RoHS日期	9AKK107992A8994
REACH Declaration	9AKK107992A8994

分类	
ETIM 8	EC001179 - Protective metallic hose
UNSPSC	39131706

分类

低压产品及系统 → 安装产品 → 电缆保护、防爆和照明 → Flexible Cable Protection Systems

