SIEMENS

Data sheet 8MF1060-2UD10-0A



SIVACON, Roof, Closed, IP40, W: 600 mm, T: 1000 mm, zinc-plated

Model	
product brand name	SIVACON
product designation	top plate
design of the product	Closed
design of the surface	zinc plated
design of the product EMC version	No
Protection class	
protection class IP	IP40
Suitability	
suitability for use for outside use	No
Product details	
product component	
● cable entry	No
● ventilation	No
Mechanical Design	
width	600 mm
depth	1 000 mm
net weight	7.2 kg
material	steel

Approvals Certificates

General Product Approval	Test Certificates	other	
CE EG-Konf. UKCA EAC	Special Test Certificate	Confirmation	Miscellaneous

other	Environment	
Miscellaneous	Siemens EcoTech	Environmental Confirmations

Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information- and Downloadcenter (Catalogs, Brochures,…)
http://www.siemens.com/lowvoltage/catalogs
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1060-2UD10-0A

Subject to change without notice
© Copyright Siemens

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/8MF1060-2UD10-0A
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1060-2UD10-0A
CAx-Online-Generator
http://www.siemens.com/cax
Tender specifications
http://www.siemens.com/specifications



last modified: 7/24/2023

Subject to change without notice
© Copyright Siemens

Subject to change without notice
© Copyright Siemens