

Han-Port Combi ins. GB(BS)/HIFF cut-out



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 001 0452
Specification	Han-Port Combi ins. GB(BS)/HIFF cut-out
HARTING eCatalogue	https://harting.com/39500010452

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Socket
Specification	2 cut-outs for HIFF data module Finger safe

Version

Termination method	Screw termination
Field of application	Great Britain (BS)

Termination data

Supply voltage	250 V AC
Nominal current	13 A
Nominal frequency	50 Hz 60 Hz

Technical characteristics

Conductor cross-section	4 mm ²
Mounting depth	30 mm

Material properties

Material (hood/housing)	Thermoplastic
-------------------------	---------------



Pushing Performance
Since 1945

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	87 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140190429
eCl@ss	27144042 Plug socket
ETIM	EC000450
UNSPSC 24.0	39121406