

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200680139](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Solid Body Splitter, 1 x 4-Pole Male to 2 x 4-Pole Females, Black Overmold

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Tees and Splitters
Series	120068
IP Rating	IP67
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Type	Splitter - Solid Body
UPC	78678886655

Physical

Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	Single
LED Indicator	No
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	29.470/g
Poles	5
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-25°C to +90°C

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC / 36V DC

Material Info

Engineering Number	081205EMF00000
--------------------	----------------

Reference - Drawing Numbers

Sales Drawing	SD-120068-032
---------------	---------------



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/01/2018 (15 January 2018) 2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120068](#) Series