

BU-0062-M-XX-*

(UL® Listed, Shrouded Right Angle Banana, PVC Test Lead)



- UL[®] Listed Test Lead
- Standard Right angle 4mm Shrouded Banana Plugs on one end. Other end is Tin dipped.
- Banana plug is Nickel plated beryillium copper and brass
- Wire is 18 AWG (65/36) UL 1855, 80°C with a chemical resistant PVC jacket. Length is designated in inches by the "XX" in the part number. Standard lengths are: 12", 18", 24", 39", 48", 60" and 72"
- Ratings: 1000 V, 20 Amps.

Hands free testing to 3000V.

- Colors: Designated by "*" in the part number: Std. Colors are: -0 black, -2 red, -4 Yellow, -5 Green, -6 Blue, -8 Gray, -9 White
- RoHS Compliant

Mueller Electric Company 1208 Massillon Rd. Ste. N-1500 Akron, OH 44306-4524

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524