

## Overview

G-007 Trail camera from SURE24. This is an Invisible 40pcs 940NM IR LED trail camera up to 75ft HD with time lapse function. This trail camera has a user friendly interface and can be used both inside and outside for security surveillance.

This trail camera is ideal for a wide range of uses including filming wildlife and the following :

- Warehouse, Storage, Farm Area Surveillance
- Home, Office And Community Security Surveillance Where Digital Evidence Is Needed
- Home And Property Security
- Farm Gates or Driveways
- Remote Crop And Live Stocks Surveillance
- Fauna Surveys
- Live Stocks Surveys and Surveillance.



## Specification

- Sensor: 8 Mega Pixels MAX, Real 5 Mega Pixels Coms
- Lens: Standard Lens, 50 Deg, PIR Detection Angle: 48 Degrees
- Infrared Light: 40 pcs no glow IR 940nm LED, up to 18 meters(59ft)
- Passive Infrared Sensor: Up to 18 meters(59ft)
- Still Image: 8 Mega Pixel max.
- Image Format: JPEG
- Photo Burst: 1-9 Burst (Programmable)
- Video 1280 x 720 Pixels/20fps With Audio
- Video Format: Motion JPEG
- Image/Video: Day: Colour Night: Black/White
- White Balance: Auto
- Exposure: Auto
- Stamp: Date/Time Stamped On Still Image/Video
- Time Lapse: 5-600 Seconds (Programmable)
- Delay Time: 5-600 Seconds (Programmable)
- Display: Status LCD
- Coverage Testing: Laser Beam To Identify The Capture Area
- Programming: Button Interface
- Manual Shutter: Yes
- Memory Expansion: Up to 32GB SD Card
- TV Out: Yes NTSC, PAL
- Communication Port USB 2.0

Battery LR14 C x 4 pcs (not included)

Power External: DC6 Vbattery pack - Separately

Dimension: 73mm dia. 142mm height