

PRODUCT-DETAILS

TC5350

LATCHING CLAMP .98X.98IN NAT NY SCR



General Information

Extended Product Type	TC5350
Product ID	7TCG009500R0042
EAN	5414363059028
Catalog Description	LATCHING CLAMP .98X.98IN NAT NY SCR
Long Description	Re-Usable Latching Cable Clamp, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 25.0mm (0.984 Inches), Width of 25.0mm (0.984 Inches), Maximum Height of 21.3mm (0.84 Inches), Screw Mounting Method, Mounting Hole Diameter of 4.3mm (0.17 Inches), 100 Pack

Ordering

EAN	5414363059028
UPC	786210620855

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	1000 piece
Package Level 2 Width	15.4 in 391 mm
Package Level 2 Height	11 in 279 mm
Package Level 2 Depth / Length	23.6 in 599 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19980621
Material	Nylon/Polyamide 6.6
Mounting Type	Screw
Number of Batteries	0
Product Name	TY-RAP FASTENING
Product Type	Latching Clamp

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC5350
Instructions and Manuals	TC5350

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121702
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5029 >> Nylon Cable Clips

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

