

TE Internal #: 6-2278526-1

TE Internal Description: 10POS,AMP MCP1.5K,REC HSG,ASSY

AMP MCP, SEALED CONNECTOR HOUSING

[View on TE.com >](#)



[All AMP MCP, SEALED CONNECTOR HOUSING \(97\)](#)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2278527-1
10POS,AMP MCP1.5K,REC HSG

Customers Also Bought



TE Part #1241380-1
AMP MCP 1.5K, CONTACT, SWS



TE Part #2334366-1
32POS, HYBRID, HDR ASSY, 90DEG, SLDR



TE Part #2385446-1
28POS, HYBRID, REC HSG ASSY, UNSLD



TE Part #2386053-2
TAB 1.2X0.6, TERMINAL, SRC, REM 1.2, 0.5MM2

TE Part #2289407-2
TRANSMISSION CABLE FOR GREATWALL



TE Part #2324105-2
50POS, MQS, SOCK HSG



TE Part #2405580-1
12POS, MCON 0.5, REC HSG, UNSLD, COD A

TE Part #2435069-3
JPT, TERMINAL, A REC 2.8 CONTACT SWS SN

TE Part #2437311-3
MCON 1.2, TERMINAL, SWS, CB, REC AG

TE Part #2498813-2
TAB CONN CVR, 66POS, HYBRID, RH

Documents

Product Drawings

10POS,AMP MCP1.5K,REC HSG,ASSY

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_6-2278526-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-2278526-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-2278526-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English