



PRODUCT-DETAILS

SPUL32/25M**32MM GS-PVC COAT CONDUIT 25M - GR****General Information**

Extended Product Type:	SPUL32/25M
Product ID:	7TCA296030R0370
EAN:	5020963009037
Catalog Description:	32MM GS-PVC COAT CONDUIT 25M - GR
Long Description:	Liquid Tight, Medium Flexibility, Covered Steel Conduit, Nominal Conduit Size 32mm, Outside Diameter 33.1mm, Inside Diameter 26.7mm, Static Bend Radius 165mm, Reel Length 25 Meters, UL Listed and CSA Approved, PVC Covered Galvanised Steel Core with Copper Packing, Grey
Display Name:	SPUL32/25M

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Flexible Protection Systems

Ordering

EAN: 5020963009037

UPC: 786210275321

Dimensions

Outside Diameter: 33.1 mm

Technical

Number of Batteries: 0

Color: Gray

Material: Galvanized Steel Core with PVC Cover and Copper Packing

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963009037

Package Level 1 Height: 9.37 in
238 mm

Package Level 1 Depth / Length: 19.25 in
489 mm

Package Level 1 Width: 19.25 in
489 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

