




Wiedergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. No rights in this or in the Patent, Gebrauchsmuster oder dessen nachträgliche Verlängerung vorbehalten. The rights in this or in the Patent, Gebrauchsmuster oder dessen nachträgliche Verlängerung vorbehalten. In case of any deviation from the original, the user shall be liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.


Die deutsche Version dieser Zeichnung dient nur zur Erleichterung der Handhabung. Bei Abweichungen von dem englischen Original gilt das englische Original. The English version of this drawing has been drawn for convenience only and may deviate from the original. In case of any deviation from the original, the user shall be liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.

Anforderungsstufe 2
performance level 2

Kontaktbereich vergoldet
mating area gold plating

Anschlussbereich verzinkt 4-6 μm
terminal area 4-6 μm tin plating

Koplanarität der Anschlüsse $\leq 0,1\text{ mm}$
coplanarity area of termination $\leq 0,1\text{ mm}$



BA 7-23 - Höhe Bauhöhe
type 7-23 - High Profile

	80	39 x	49,53	53,95 $\pm$ 0,03	55,88	52,55	51,55	0	17,76	72	
	68	33 x	41,91	46,33 $\pm$ 0,03	48,26	44,93	43,93	0	17,76	72	
2524143-3	50	24 x	30,48	34,9 $\pm$ 0,03	36,83	33,5	32,5	0,635	17,76	56	VPE: 160 Stück PU: 160 pcs
	40	19 x	24,13	28,55 $\pm$ 0,03	30,48	27,15	26,15	0	17,76	56	
2524143-1	32	15 x	19,05	23,47 $\pm$ 0,03	25,4	22,07	21,07	0	17,76	44	
	26	12 x	15,24	19,66 $\pm$ 0,03	21,59	18,26	17,26	0,635	17,76	44	
	20	9 x	11,43	15,85 $\pm$ 0,03	17,78	14,45	13,45	0	7,6	32	
	16	7 x	8,89	13,31 $\pm$ 0,03	15,24	11,91	10,91	0	7,6	32	
2524143-2	12	5 x	6,35	10,77 $\pm$ 0,03	12,7	9,37	8,37	0	7,6	24	
Ident-Nr. part-no.	Polzahl pin	n x	A	B	C	D	E	F	G	H	Bemerkung remark

Dimension no.
Information:
Anforderungsstufe 247 / class 247
Sonderclip / special clip

Customer drawing:
This Drawing is a
controlled Document

1
Index

29.01.2026
Date

Tolerances
Dim. for Information
ISO 8015

Subject to modification without
prior notice.
Drawing will not be updated.

TE Connectivity

Scale: 5:1
Material

AMPSMC
Female Straight
B SMT Type 7-23
C-2524143

C
A2

Verpackt im Gurt in Anlehnung an DIN IEC 60286-3
tape on reel packaging according to DIN IEC 60286-3
Verpackungseinheit: 170 Stück
packaging unit: 170 pcs