



Mounting rails vertical busbar 30 x 30 mm, L: 1610 mm, 1 set = 4 units

Model	
product brand name	SIVACON
product designation	standard mounting rail
design of the product	30x30
type of busbar profile	shaped
General technical data	
number of poles	4
short-circuit current rating	50 kA
position of main busbar	Top
Main circuit	
operational current rated value	970 A
Mechanical Design	
height	1 610 mm
width	30 mm
width of the busbar	30 mm
depth	30 mm
installation width	200 mm
mounting height	1 610 mm
installation location	busbar space
thickness of the busbar	30 mm
busbar center-to-center spacing	40 mm
net weight	23.29 kg
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

other	Environment
-------	-------------

[Miscellaneous](#)

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ4000-0BA27>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ4000-0BA27>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ4000-0BA27

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/15/2025 

