

WXD 2010

2-Channel Solder- and Desoldering Station Set, 200 W (255 W)
Product no.: T0053428699N



Benefits

- › Desoldering station WXD 2, 2 channels with desoldering iron WXDP 120
- › Soldering- and desoldering tools with intelligent WX technology
- › Connection to external compressed air supply required
- › Energy effective: automatic stand-by mode for tools
- › Patented, ESD safe glass display. Simple and fast setting of soldering parameter.





Technical Data

Dimensions L x W x H (mm)	174 x 154 x 135
Dimensions L x W x H (inches)	6,69 x 5,94 x 5,12
Weight (approx.) in kg	3.2
Voltage	230 V, 50 Hz
Power	200 W (255 W)
Channels	2
Temperature range (depends on tool) °C	50 - 550
Temperature range (depends on tool) °F	150 - 999
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding socket	Via 3, 5 mm pawl socket on back of unit.
Display	255 x 128 dots / Backlighting
Air consumption l/min	35
Operating pressure in bar/psi	4,0 - 6,0 / 58 - 87
Capacity l/min	---
Vacuum	55 kPA (8 psi)