


① only for four indent crimping tool adjusting  $\varnothing 0,1$



part no.		$\varnothing D$	wire gauge		stripping length	
silver plated	gold plated		mm <sup>2</sup>	AWG		
09 15 000 6104	09 15 000 6124	0,90	0,14-0,37	26-22	8	
09 15 000 6103	09 15 000 6123	1,10	0,5	20		
09 15 000 6105	09 15 000 6125	1,30	0,75	18		
09 15 000 6102	09 15 000 6122	1,45	1	18		
09 15 000 6101	09 15 000 6121	1,75	1,5	16		
09 15 000 6106	09 15 000 6126	2,25	2,5	14	6	
09 15 000 6107	09 15 000 6127	0,90	0,14-0,37	26-22	8	①

	All rights reserved		Scale 2:1	Free size tol.	Ref. Sub. TB 09 15 000 61. v. 22.03.99		
	Department EL PD - DE		Created by RULLKOETTER	Inspected by SCHNIEDER	Standardisation TIEMANNA	Date 2014-05-20	State Final Release
HARTING Electric GmbH & Co. KG D-32339 Espelkamp			Title Han D crimp contacts male			Doc-Key / ECM-Nr. 100086611/UGD/006/A 500000075030	
			Type TB	Number 09 15 000 61XX		Rev. A	Page 1/1