

## Datasheet

# Heating Element Drum Heater - Polyurethane Nylon 1250mm 460mm

RS Stock number 798-3729



### Description

The HISD is manufactured from lightweight but resilient materials and fitted with adjustable quick release buckles for ease of installation and removal. Temperature is regulated via an in-built thermostat up to a maximum of 90°C for plastic drums. Jackets with higher power ratings and 0-120°C thermostat can be manufactured for use with metal drums.

These jackets are ideally suited for the warming of a variety of products including fats, oils and foodstuffs.

### Technical Specification

- **Power rating:** 110 or 230 Volts, Power as below
- **Temperature Control:** 0 to 40°C or 0 to 90°C thermostat

Size:	Wattage:	Drum Size:
400mm x 1020mm	200 Watts	25L
460mm x 1250mm	250 Watts	50L
370mm x 1650mm	400 Watts	105L
450mm x 1950mm	450 Watts	200L
800mm x 1950mm	1200 Watts	200L

### Features and Benefits

- Teflon/Polyester Insulated
- Class II Double Insulation
- IP40 Protection
- **0 to 90°C thermostat**
- Thermal Insulation
- Standard Sizes  
25L, 50L, 105L, 200L
- Adjustable Quick Release Buckles
- 4 Metre Power Cable

### Applications

- HISD heater is the ideal solution for heating liquid materials stored in metal or plastic drums.