



Main

Range of product	Mureva Styl
Range	Mureva Styl
Product or component type	Push-button with pilot lamp
Category	Push-button with pilot lamp
Device presentation	Insert
Colour tint	Grey (RAL 7016)

Complementary

Device mounting	Surface Flush
Switch function	Double push-button
Actuator	Push-button
Rated current	10 A
[Ue] rated operational voltage	250 V AC
Local signalling	LED blue
Current consumption	0.15 mA 250 V
Condition of use	Indoor/Outdoor
Material	SEBS PC (polycarbonate) Brass
Fixing mode	Screwless
Clamping connection capacity	1.5...2.5 mm ² rigid 1.5...2.5 mm ² flexible 1.5...2.5 mm ² stranded
Wire stripping length	13 mm
Length	71 mm
Height	40 mm
Width	71 mm
Embedding depth	10 mm
Projecting depth	60 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Quality labels	CE AENOR EAC NF
IP degree of protection	IP55
IK degree of protection	IK07
Flame retardance	Self-extinguishing ≥ 650 °C according to IEC 60695-2-1
Standards	EN 60669-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C