

# Rittal – The System.

Faster – better – everywhere.

## ► Baying enclosure system VX25 Basic enclosure – VX 8005.000

Date : Jun 14, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Baying enclosure system VX25 Basic enclosure – VX 8005.000

created: 14.06.2019 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Product description

<b>Material:</b>	Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Gland plates: Sheet steel, 1.5 mm Mounting plate: Sheet steel 3.0 mm
<b>Surface finish:</b>	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	IP 55
<b>Protection category NEMA:</b>	NEMA 12
<b>Type rating to UL 508A:</b>	Type 1,12
<b>IK Code:</b>	IK10
<b>Supply includes:</b>	Enclosure frame Door(s) Door hinged on the right, may be swapped to the left Roof plate Rear panel Gland plates Mounting plate 2 punched rails 18 x 39 mm Lock: 3 mm double-bit

**Basic material:** Sheet steel

## Product features

**Dimensions:** Width: 1000 mm  
Height: 2000 mm  
Depth: 500 mm

**Mounting plate:** Width: 899 mm  
Height: 1896 mm

**Number of doors:** 2

**Packs of:** 1 pc(s).

**Weight/pack:** 157.1 kg

**EAN:** 4028177813540

**Customs tariff number:** 94032080

**ETIM 6.0:** EC000261

**ETIM 5.0:** EC000261

**eCl@ss 8.0/8.1:** 27180101

**eCl@ss 7.0/7.1:** 27180101

**eCl@ss 6.0/6.1:** 27180101

**eCl@ss 5.1/5.1.4:** 27180101

**Product description:** VX Baying enclosure system, WHD: 1000x2000x500 mm, sheet steel, with mounting plate, two doors at the front

## Approvals

**Approvals:** CSA  
Lloyds Register of Shipping  
UL + C-UL

**Certificates:** EAC  
Protection category

**Declarations:** Declaration of conformity