

### FR50 - Bizflame Work FR Coverall

**Collection:** Bizflame™ Work

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Bizflame Work: 99% Cotton, 1% Carbon Fibre, 350g

**Outer Carton:** 10



### Product information

This coverall is perfect for the demands of the offshore industry. Constructed with a highly innovative flame-retardant fabric with high visibility reflective tape double stitched for enhanced visibility. Meeting all the required EN standards, features include triple stitched seams, high visibility strips on shoulders, arms and legs, concealed 2-way front brass zip and two front slant chest pockets with concealed brass zips.

#### Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

#### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

### Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 2 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 8.6 CAL/CM<sup>2</sup>, ATPV 9.8 CAL/CM<sup>2</sup>)

IEC 61482-2 IEC 61482-1-2 APC 1

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV=13.6 Cal/CM<sup>2</sup> (HAF=82%))

### Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Hook and loop cuffs for a secure fit
- Action back for extra freedom of movement
- Concealed zip pocket
- Available in sizes from XS to 6XL
- Triple-stitched seams for extra durability
- 10 pockets for ample storage
- 40+ UPF rated fabric to block 98% of UV rays

**FR50 - Bizflame Work FR Coverall**  
**Commodity Code: 6211321000**

**Test House**

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)  
 Bracetown Business Park  
 D15 YN2P, Ireland  
 Cert No: 2777/13136-03/E00-00

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)  
 Sebenhirtenstrasse 12A  
 1230, Austria  
 Contact: Marion Pfeiler  
 Cert No: 0598

**Wash Care**



**Carton Dimensions/Weight**

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
FR50GNRXS	Green	43.0	28.0	50.0	1.5600	0.0602	5036108406791	25036108892000
FR50GNRS	Green	43.0	28.0	50.0	1.5600	0.0602	5036108406777	25036108891980
FR50GNRM	Green	43.0	28.0	50.0	1.5600	0.0602	5036108406760	25036108891973
FR50GNRL	Green	43.0	28.0	50.0	1.5600	0.0602	5036108406753	25036108891966
FR50GNRXL	Green	43.0	28.0	50.0	1.5600	0.0602	5036108406784	25036108891997
FR50GNRXXL	Green	43.0	28.0	50.0	1.5600	0.0602	5036108406807	25036108892017
FR50GNRXXXL	Green	43.0	28.0	50.0	1.5600	0.0602	5036108406814	25036108892024
FR50GNR4XL	Green	43.0	28.0	50.0	1.5600	0.0602	5036108406746	25036108891959