Compact guide cylinder – JMGP Series Ø 12, Ø 16, Ø 20, Ø 25, Ø 32, Ø 40, Ø 50, Ø 63, Ø 80, Ø 100

Weight
Max. **69** %*1 **reduction**
0.32 kg ➡ **0.1 kg**


Overall length
Max. **31** %*2 **reduction**
100 mm ➡ **69.5 mm**

Height
33 %*2 **reduction**
48 mm ➡ **32 mm**

*1 Compared with the existing MGP-Z series, Ø 16, 10 mm stroke *2 Compared with the existing MGP-Z series, Ø 32, 25 mm stroke

Overall length shortened

JMGP Ø 32



Existing model Ø 32

Height shortened

JMGP Ø 32



Existing model Ø 32

Suitable for pushing, lifting, or clamping in a transport line

