

## niroflex easyfit

PRODUCTSHEET

### ■ niroflex easyfit hand glove

Colour Code / Size	Weight	Item number	Item number detectable version
brown: 5 - 5,5 / XXS	0,18 kg	GS 101 000 0001	GS 141 000 0001
green: 6 - 6,5 / XS	0,19 kg	GS 101 100 0001	GS 141 100 0001
white: 7 - 7,5 / S	0,21 kg	GS 101 110 0001	GS 141 110 0001
red: 8 - 8,5 / M	0,23 kg	GS 101 120 0001	GS 141 120 0001
blue: 9 - 9,5 / L	0,26 kg	GS 101 130 0001	GS 141 130 0001
orange: 10 / XL	0,27 kg	GS 101 140 0001	GS 141 140 0001
olive: 11 / XXL	0,32 kg		GS 141 150 0001

Material: Stainless steel  
 Ring diameter: 4,2 mm  
 Wire gauge: 0,55 mm



### ■ niroflex easyfit glove 75 mm cuff

Colour Code / Size	Weight	Item number	Item number detectable version
brown: 5 - 5,5 / XXS	0,3 kg	GS 101 000 7001	
green: 6 - 6,5 / XS	0,31 kg	GS 101 100 7001	
white: 7 - 7,5 / S	0,33 kg	GS 101 110 7001	
red: 8 - 8,5 / M	0,35 kg	GS 101 120 7001	
blue: 9 - 9,5 / L	0,38 kg	GS 101 130 7001	
orange: 10 / XL	0,39 kg	GS 101 140 7001	
olive: 11 / XXL	0,91 kg		GS 141 150 7001

Material: Stainless steel  
 Ring diameter: 4,2 mm  
 Wire gauge: 0,55 mm



Ambidextrous



easyfit also available  
 in a detectable version



DIN EN 1082-1  
 DIN EN 14328  
 DIN EN 1811  
 ISO 13999-1



## niroflex easyfit

PRODUCTSHEET

### ■ niroflex easyfit glove 190 mm cuff

Colour Code / Size	Weight	Item number	Item number detectable version
brown: 5 - 5,5 / XXS	0,4 kg	GS 101 001 9001	GS 141 001 9001
green: 6 - 6,5 / XS	0,42 kg	GS 101 101 9001	GS 141 101 9001
white: 7 - 7,5 / S	0,44 kg	GS 101 111 9001	GS 141 111 9001
red: 8 - 8,5 / M	0,46 kg	GS 101 121 9001	GS 141 121 9001
blue: 9 - 9,5 / L	0,49 kg	GS 101 131 9001	GS 141 131 9001
orange: 10 / XL	0,52 kg	GS 101 141 9001	GS 141 141 9001
olive: 11 / XXL	0,59 kg		GS 141 151 9001

Material: Stainless steel  
 Ring diameter: 4,2 mm  
 Wire gauge: 0,55 mm



### ■ niroflex easyfit Full arm

Colour Code / Size	Weight	Item number	Item number detectable version
brown: 5 - 5,5 / XXS	0,85 kg	GS 121 000 0001	GS 131 000 0001
green: 6 - 6,5 / XSS	0,95 kg	GS 121 100 0001	GS 131 100 0001
white: 7 - 7,5 / S	1,15 kg	GS 121 110 0001	GS 131 110 0001
red: 8 - 8,5 / M	1,2 kg	GS 121 120 0001	GS 131 120 0001
blue: 9 - 9,5 / L	1,23 kg	GS 121 130 0001	GS 131 130 0001
orange: 10 / XL	1,25 kg	GS 121 140 0001	GS 131 140 0001
olive: 11 / XXL	1,27 kg		GS 131 150 0001

Material: Stainless steel  
 Ring diameter: 4,2 mm  
 Wire gauge: 0,55 mm

