

FEATURES

- Black polyester coated stainless steel
- Releasable and re-usable
- Excellent resistance to corrosion, radiation and abrasion
- Flame retardant
- Highly durable with excellent chemical resistance

RS PRO Metallic 316 Stainless Steel Releasable Cable Tie, 450mm x 10 mm

RS Stock No.: 547-4406



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO stainless steel grade 316 coated releasable cable ties have been designed for use in Industrial and Marine environments. These ties are an ideal alternative where Nylon 66 cable ties are not suitable such as harsh environments or places where there is heat. The stainless steel used has a high resistance to damage by chemicals and salts making them suitable for harsh environments.

General Specifications

Type	Releasable
Colour	Metallic
Material	316 Stainless Steel
Application	Bundling wire together, applications in industries such as: Oil and gas, Marine, Chemical
Resistant To	Chemical resistance
Minimum Operating Temperature	-80°C
Maximum Operating Temperature	150°C
Fire Behaviour	Flame Retardant
Quantity	100

Mechanical Specifications

Length	450mm
Width	10mm
Tensile Strength	850N

Approvals

Standards Met	ABS, DNV, Lloyd's Register, UL
---------------	--------------------------------



Datasheet

Non-Releaseable Stainless Steel Cable Tie

RS Part No.	Length mm	Width mm	Max Bundle Dia
1595329	360	4.6	100
1595313	200	7.9	50
1595357	150	4.6	50
1595335	360	7.9	100
5474305	520	4.6	150
5474311	520	7.9	150
7436162	680	4.6	200
7436166	380	7.9	200
7436172	1000	4.6	300
7436178	840	7.9	250
7436181	1000	7.9	300

Coated Stainless Steel Cable Tie

RS Part No	Length mm	Width mm	Max Bundle Dia
5474327	150	4.6	50
5474333	360	4.6	100
5474349	250	4.6	150
5474355	200	7.9	50
5474377	360	7.9	100
5474383	520	7.9	150