

Material:

- Perbunan

Characteristic feature:

- Shore: 70 ± 5


Feature:

The O-ring must be mounted into the first groove of the conduit

The conduit, with its pre-mounted sealing ring, must be inserted into the SEM gland and simply twisted into the end.

Temperature Range
-25 to 100°C (-13 to 212°F)

Fits for NW	Internal Diameter mm	Thickness mm	Cat. No.	Std. Pk.
8.5	9.0	1.0	8112600	100
10	8.9	1.25	8112601	100
12	8.5	1.5	8112602	100
13	8.1	1.6	8112603	100
14	12.5	1.5	8112604	100
17	15.0	1.5	8112605	100
22	15.0	1.5	8112606	100
23	17.0	2.5	8112607	100
29	23.0	2.5	8112608	100
37	23.0	2.5	8112609	100
50	31.0	2.5	8112610	100



Clamping clip for conduit tubes

Material:

- Polyamide

Color:

- Black

Temperature Range
-25 to 100°C (-13 to 212°F)

Suitable for NW	L mm	H mm	D mm	Cat. No.	Std. Pk.
8.5/10	30.0	23.0	13.0	8218102	100
12/13	30.0	23.0	13.0	8218137	100
14	31.0	24.0	13.0	8218140	100
17	35.0	30.0	15.0	8218170	100
22/23/26	42.0	38.0	16.0	8218234	100
29	51.0	49.0	16.0	8218293	50
37	61.0	51.0	18.0	8218374	50
50	74.0	64.0	19.0	8218501	50

