

TevuChem® 765



APPLICATION

- › oil production
- › petrochemicals
- › printing works
- › metal processing
- › recycling work

QUALITIES AND ADVANTAGES

- › outstanding grip
- › very good chemical resistance to mineral oils and aliphatic carbohydrates
- › liquid-tight
- › good mechanical properties

CHEMICAL PROTECTIVE GLOVES



Article no.	765
Name	TevuChem® 765
Material	nitrile, special nitrile, cotton
Description	liner, cuff, multi-layer composition
Length (mm)	290 - 310
Total thickness (mm)	1,45 ± 0,25
Colour	yellow/dark blue
Size	8, 9, 10, 11
Classification	category III
	EN 388:2016 EN 374-1:2016/Type A EN 374-5
	3111X JKLOPT Virus



FEATURES

- › AQL < 0,65
- › 2-layer system
- › ergonomic fit
- › high-quality cotton liner
- › free from natural latex

www.kcl.de
sales@kcl.de



by Honeywell

KCL GmbH

Industriepark Rhoe
Am Kreuzacker 9
36124 Eichenzell
Germany
Phone +49 6659 87-300
Fax +49 6659 87-318

Honeywell