

1580

Tool trolley

with 4 drawers

Code	ETIM
6627550	EC011808
EAN	UNSPSC
4010886662755	56-12-18-02
Country of origin	eCl@ss
Germany	21-07-11-00
Customs tariff number	
94032080	



Article description

- Body:
- Dimensions: H 930 x W 625 x D 400 mm
- Double sided metal shutters to secure the whole internal space
- Worktop with tough ABS plastic plate
- Manoeuvrable and easy to steer with drive/steer handle
- Side walls with Euro perforation 10 x 38 mm for attaching hooks and tools
- Safety through heel protection and all-round impact protection for people and the environment
- Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
- Drawers:
- Central locking with cylinder lock
- 4 wide drawers (W 480 x D 325 x H 45 mm), all drawers extendable on both sides
- 1 large capacity storage compartment in the bottom
- Ball-bearing guide rails, with middle and end catches
- Can be individually equipped with lengthwise and crosswise dividers (can be ordered individually)
- Load capacity per drawer 20 kg
- Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
- GEDORE chassis:
- Total load capacity 300 kg
- 2 high-performance wheels on roller bearings (fixed castors Ø 140 mm)
- 2 GEDORE easy-running wheels with ball bearings (swivel castors, 100 mm), one of them with total brake each
- The GEDORE trapezoidal axle construction secures smooth running, manoeuvrability and track-keeping also in case of maximum loads
- Accessories:
- Options:
- Can be equipped with GEDORE tool modules (1500 ES/1500 CT)
- Can be extended as required with GEDORE attachment chest No. 1430
- Special colours and designs on request
- Delivery without tools and accessories

Article information

Contents (Qty of pieces)	1	Number of lengthwise dividers	3
Version/Execution	All drawers open either side	Number of drawers	4
Net weight [kg]	41 kg	Load capacity per drawer [kg]	20 kg
Total length [mm]	400 mm	Drawer type	4x H. x B. x T. = 45 x 480 x 325 mm plus Großraumstaufach
Total width [mm]	625 mm	Single pull-out stop	no
Total height [mm]	930 mm	Number of wheels	4
Material	sheet steel	Working height	930
Surface	powder-coated	Static load carrying capacity [kg]	300 kg
Colour	RAL 5017	RAL colour tone	blue
Dimension (L x W x H)	400 mm x 625 mm x 930 mm	Fixed roller diameter (2x)	140
Number of crosswise dividers	2	Swivel castor diameter with brakes (2x)	100