

WMS-OT HF 2,4 (EX4)R - Marking sleeve



1163127

<https://www.phoenixcontact.com/in/products/1163127>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marking sleeve, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, THERMOMARK W, unperforated, mounting type: slide-on, cable diameter range: 1 ... 2.4 mm, Number of individual labels: 1, text field height: 4 mm, text field width: 30000 mm

Your advantages

- Permanent and captive identification of single-core wires, wires, cables, pneumatic hoses, and other cylindrical objects
- Non-shrinkable halogen-free marking sleeve on rolls, in an oval design, for marking conductors and cables
- The oval design and the large opening enable rapid fitting onto the conductor or cable
- Through the use of the cutting or perforation unit, the marking sleeve can be cut to or perforated at the desired length (max. 1 m)
- Widely used and proven worldwide in the railway industry

Commercial data

Item number	1163127
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG2
Product key	BGE22F
GTIN	4063151174552
Weight per piece (including packing)	245 g
Weight per piece (excluding packing)	239 g
Customs tariff number	39173200
Country of origin	CN

WMS-OT HF 2,4 (EX4)R - Marking sleeve



1163127

<https://www.phoenixcontact.com/in/products/1163127>

Technical data

Notes

Material information	For the THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK ROLLMASTER 300/600, and THERMOMARK E.300 (D)/E.600 (D) roll printers, this material can only be processed with an external media hub.
----------------------	--

Product properties

Product type	Conductor marking
Area of application	Railway industry

Marking

Number of individual labels	1
Identification technology	Thermal transfer for rolls

Dimensions

Width	4 mm
Text field width	30000.00 mm
Text field height	4.00 mm
Length	30 m

External dimensions

Outside diameter	1 mm ... 2.4 mm
------------------	-----------------

Material specifications

Color	white (RAL 9010)
Material	Polyolefine
Flammability rating according to UL 94	V0
Base element material	polyolefine
Components	halogen-free

Cable/line

External cable diameter	1 mm ... 2.4 mm
-------------------------	-----------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
---------------	-------------------------------------

WMS-OT HF 2,4 (EX4)R - Marking sleeve



1163127

<https://www.phoenixcontact.com/in/products/1163127>

Result	Test passed
--------	-------------

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Specification	IEC 60068-2-2:2007-07
Result	Test passed
Duration	96 h
Temperature for testing	120 °C

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	ISO 22479:2019-05
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-30 °C ... 125 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	5 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	slide-on
---------------	----------

WMS-OT HF 2,4 (EX4)R - Marking sleeve



1163127

<https://www.phoenixcontact.com/in/products/1163127>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

WMS-OT HF 2,4 (EX4)R - Marking sleeve



1163127

<https://www.phoenixcontact.com/in/products/1163127>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

WMS-OT HF 2,4 (EX4)R - Marking sleeve

1163127

<https://www.phoenixcontact.com/in/products/1163127>



Accessories

THERMOMARK ROLL 2.0 - Thermal transfer printer

1085260

<https://www.phoenixcontact.com/in/products/1085260>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK ROLL-CUTTER - Cutter

5146422

<https://www.phoenixcontact.com/in/products/5146422>



Cutter for THERMOMARK ROLL and THERMOMARK ROLL 2.0, cutter width: 110 mm, suitable for: TML, SK, EML-RM, PMM, WMS, WMS-2 HF, WMS-OT HF, TMT continuous media, and EMT (EX15)R

WMS-OT HF 2,4 (EX4)R - Marking sleeve

1163127

<https://www.phoenixcontact.com/in/products/1163127>



THERMOMARK ROLL-CUTTER/P - Cutter

5146435

<https://www.phoenixcontact.com/in/products/5146435>



Perforation cutter, for the THERMOMARK ROLL and THERMOMARK ROLL 2.0, cutter width: 45 mm, suitable for: WMS continuous media up to 25.4 mm, WMS-2 continuous media up to 25.4 mm, WMS-OT HF continuous media, TMT continuous media, and EMT (EX15)R

THERMOMARK-RIBBON 110-WMSU - Ink ribbon

0801358

<https://www.phoenixcontact.com/in/products/0801358>



Ink ribbon, For roll printer for printing product groups WMS..., WMS-2 HF..., and WMTB HF-HP, length: 300 m, roll length: 300 m, width: 110 mm, color: black

WMS-OT HF 2,4 (EX4)R - Marking sleeve

1163127

<https://www.phoenixcontact.com/in/products/1163127>



THERMOMARK-RIBBON 64-WMSU - Ink ribbon

0801360

<https://www.phoenixcontact.com/in/products/0801360>



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF...,
length: 300 m, roll length: 300 m, width: 64 mm, color: black

THERMOMARK-RIBBON 25-WMSU - Ink ribbon

0803390

<https://www.phoenixcontact.com/in/products/0803390>



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF...,
length: 300 m, roll length: 300 m, width: 25 mm, color: black

WMS-OT HF 2,4 (EX4)R - Marking sleeve

1163127

<https://www.phoenixcontact.com/in/products/1163127>



TM-RIBBON 40 BK 105 - Ink ribbon

1259008

<https://www.phoenixcontact.com/in/products/1259008>



Ink ribbon, for the E-WMS... product group in combination with the THERMOMARK E.SLEEVE applicator and the WMS... and WMS-2 HF... product groups in combination with conventional roll printers, length: 300 m, roll length: 300 m, width: 40 mm, color: black

THERMOMARK ROLL-ERH - Media hub

5146448

<https://www.phoenixcontact.com/in/products/5146448>



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

WMS-OT HF 2,4 (EX4)R - Marking sleeve

1163127

<https://www.phoenixcontact.com/in/products/1163127>



THERMOMARK-ERH 500 - Media hub

5146309

<https://www.phoenixcontact.com/in/products/5146309>



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

THERMOMARK ROLLMASTER 300 - Thermal transfer printer

0804501

<https://www.phoenixcontact.com/in/products/0804501>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

WMS-OT HF 2,4 (EX4)R - Marking sleeve

1163127

<https://www.phoenixcontact.com/in/products/1163127>



THERMOMARK ROLLMASTER 600 - Thermal transfer printer

0804663

<https://www.phoenixcontact.com/in/products/0804663>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/in/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

WMS-OT HF 2,4 (EX4)R - Marking sleeve

1163127

<https://www.phoenixcontact.com/in/products/1163127>



THERMOMARK X1.2 - Thermal transfer printer

5146231

<https://www.phoenixcontact.com/in/products/5146231>



Thermal transfer printer, weight: 10 kg, length: 0.446 m, width: 242 mm, height: 274 mm, color: gray

THERMOMARK W2 - Thermal transfer printer

5146147

<https://www.phoenixcontact.com/in/products/5146147>



Thermal transfer printer for material off the roll, incl. Euro/US power cable, USB cable, and perforation knife. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English.

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in