

482.6 mm (19") installation system

482.6 mm (19") installation

Drawer, 2 U, 3 U

for a 482.6 mm (19") mounting level

For front attachment to mounting angles, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts. The small version of the 2 U variant is also suitable for mounting inside a swing frame.

Material:
Sheet steel

Colour:
RAL 7035

Supply includes:
Fully assembled, including assembly parts.

Height	Clearance openings		Installation depth mm	Packs of	Model No. DK
	Width mm	Depth mm			
2 U	411	244	250	1	7282.135
2 U	411	419	427	1	7282.035
3 U	411	419	427	1	7283.035



Drawer for 482.6 mm (19")

with shelf

For keyboards, operating manuals etc. The perforated plate in the base helps air to circulate in the enclosure. Load capacity 50 kg. The 1 U drawer can be installed rotated through 180° about its longitudinal axis, allowing it to be used as a utility table.

Material:
– Drawer: Aluminium
– Telescopic slides: Sheet steel

Surface finish:
– Drawer: Anodised
– Telescopic slides: Zinc-plated

Supply includes:
Telescopic slides.

U	Packs of	Model No. PS
1	1	4541.000
3	1	4542.000

! Also required:

Installation kit for enclosure system TS or installation kit, depth variable, see page 753.



Installation kit

for component shelves and drawers, with 482.6 mm (19") Installation in TS

For installation between the front and rear adaptor sections or adaptor pieces, 482.6 mm (19") in 600 mm wide enclosures.

Material:
Sheet steel

Surface finish:
Zinc-plated

Supply includes:
Assembly parts.

For enclosure system TS

For enclosure depth mm	Packs of	Model No. TS
600	1 set	8800.560
800	1 set	8800.580

! Also required:

- Adaptor sections, 482.6 mm (19"), see page 741, or
- Adaptor pieces, 482.6 mm (19"), see page 742.



Installation kit, depth-variable

for 482.6 mm (19") component shelves and drawers

Depending on the distance between the two 482.6 mm (19") mounting levels, the installation kit is screw-fastened in the depth between the cranked, L-shaped mounting angles or 482.6 mm (19") mounting frame. Also suitable for TE.

Material:
Sheet steel

Surface finish:
Zinc-plated

Supply includes:
Assembly parts.

Rittal Catalogue 33/System accessories

482.6 mm (19") distance between levels mm	Packs of	Model No. DK
550 – 850	2	7063.850

