

PICCOLO ABS F 85 G



Sample photo

Order symbol: ABS F 85 G
Product nbr: 8784312
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074002259
EI. number:
 Finland: 3423465
 Electric No. Denmark: 8212001954
 Electric No. Italy: 7211045
 Electric No. Sweden: 2536723

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

| Dimensions: | Length | Width | Height | Accessories: |
|-------------|--------|-------|--------|--|
| mm: | 230 | 80 | 85 | FM-3 FP 22040 |
| inch: | 9.1 | 3.1 | 3.3 | DIN-35 Mounting rail Wall fastening lug (2 pcs) |

| Materials: | Rating: |
|---|--|
| Material: ABS | Ingress Protection (EN 60529): IP66/IP67 |
| Base colour: RAL 7035 -light grey | Impact Resistance (EN 62262): IK07 |
| Cover screws material: Polyamide | Electrical insulation: Totally insulated |
| Cover colour: RAL 7035 -light grey | Halogen free (DIN/VDE 0472, Part 815): 1 |
| Cover screws colour: Grey | Flammability Rating: UL 94 HB |
| Gasket material: Polyurethane | Glow Wire Test (IEC 695-2-1) °C: 650 |
| | NEMA Class: NEMA 1, 4X, 6, 12, 13 |

Temperatures:

| | |
|------------------------------|----------------|
| Temperature °C (short term): | -40 ... 80 °C |
| Temperature °C (continuous): | -40 ... 60 °C |
| Temperature °F (short term): | -40 ... 175 °F |
| Temperature °F (continuous): | -40 ... 140 °F |

Accessories:

| | |
|------|----------------|
| F-MP | Mounting plate |
|------|----------------|

