

## Datasheet

# RS Pro Incandescent V10994 Series Beacon, Rotating, Surface Mount, 12 V dc, 24 V dc

RS Stock No: **235-433**



## Product Details

RS Pro high rotation filament beacon provides great visibility through incandescent lighting for all applications. The beacon has 12/24 V dc voltage rating depending on bulb selected. Beacon has a strong construction with IP56 degree of protection. It measures 203 x 130 mm. It features reverse polarity protection and supports operating within the temperature range of -30 to +50°C. The beacon has an optional DIN mounting stem for use with flexible DIN version.

## Features and Benefits

- A high speed (180 rpm) rotating filament beacon offers excellent visibility for all applications
- 12/24 V dc depending on bulb selected
- Current consumption: 4.6/3 A at 12/24 V
- Reverse polarity protection
- IP56 rated
- Operating temperature range: -30 to +50°C
- Magnetic versions rated to 70 mph
- Optional DIN mounting stem for use with flexible DIN version



ENGLISH

### Specifications:

Bulb Type	Incandescent
Current Type	DC
Housing Colour	Black
Lamp Included	No
Lens Colour	Lens Not Included
Light Effect	Rotating
Special Features	Low Noise Operation
Standards Met	EMC; RoHS Compliant
Base Diameter	130 mm
Current Consumption	4.6/3 A
Height	186 mm
Maximum Temperature	+50°C
Minimum Temperature	-30°C
IP Rating	IP56
Mounting Style	Single Point
Supply Voltage	12/24 V dc
Flash Rate	180 fp/min