

Main

Range	New Unica
Product or component type	Loudspeaker socket
Device application	Media device support
Device presentation	Mechanism
Colour tint	Anthracite (RAL 7021)

Complementary

Socket number	1
Number of modules	2 modules
Connections - terminals	2 pressure fixing
Fixing mode	Clip-in
Material	Thermoplastic ABS-UV stabilised
Surface finish	Painted powder coated
Depth	32 mm
Width	45 mm
Height	45 mm
Net weight	0.034 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IP degree of protection	IP2XC
IK degree of protection	IK02
Ambient air temperature for operation	5...45 °C
Ambient air temperature for storage	-5...50 °C

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins