

Datasheet

ENGLISH

External power supplies

AC/DC Single Output Desk top Type 90 Watts. ED1096 Series



Features

- Input range 11 to 16V DC
- Energy saving compact design
- RoHS Compliance
- · Cigar Input
- USB Port (+5V @ 0.8A max) Output
- Over voltage and over current protection
- MTBF: >30,000 hours

Electrical Specifications

RS STOCK NO.	MODEL OUTPUT	VOLTAGE (Vo)	MAX. LOAD (Lo)	POWER (Watts)	LOAD REGULATION	LINE REGULATION	RIPPLE & NOISE
417-906	ED1096A(01)	16V	5A	80W	+/- 5%	+/- 1%	1.2%
417-916	ED1096B(03)	19V	4.7A	90W	+/- 5%	+/- 1%	1.2%
417-900	ED1096D(01)	24V	3.75A	90W	+/- 5%	+/- 1%	1.2%

NOTE

Electrical Specifications

INPUT

- Input Range 11 to 16VDC
- Input Current ≤10A
- Efficiency 87% Typ.

OUTPUT


• Short Circuit Protection Latch off


ENVIRONMENTAL


- Operating Temperature 0 to 40°C
- Storage Temperature -20 to 85 °C
- Storage Humidity 5 % to 95%


SAFETY and EMC

• e1, FCC









- Case Size: 105.9Lx51.5Wx18.4H (mm)
- Weight: 220g

4.75 / 1.75 / 11.00mm



5.5 / 2.1 / 10.50mm



5.5 / 2.5 / 12.5mm



6.3 / 3.0 / 12.00mm



RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

^{13.} Ripple & noise is measured by using 20MHz bandwidth limited oscilloscope and terminated each output with a 0.1uf ceramic capacitor & parallel with 47uF aluminum capacitor at full load and nominal line.