



tesafilm® crystal clear

Product Information

BNR 57759, 57758, 57726, 04102, 57790, 57766, 57315, 57330, 58260, 58244, 57329, 57316, 57767, 57418, 57417, 58245, 58259, 57710, 59424, 57859, 57318, 57470, 57319, 57725, 57320

Product Description

tesafilm® crystal clear marks the premium class among the self-adhesive tapes from tesa®. This clear tape is tear-resistant and offers extra strong adhesion.

Product Features

- Outstanding transparency
- Invisible on almost all surfaces
- Strong adhesion
- High age-resistance
- Silent unwinding
- PP-foil and solvent-free adhesive
- Suits all available tesafilm® dispensers

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|---------------------|-------------------|-------|
| • Backing | BOPP | • Total thickness | 55 µm |
| • Type of adhesive | water-based acrylic | | |

Properties/Performance Values

- | | | | |
|--------------------------|--------------------|--|------------------|
| • Tensile strength | 31 N/cm | • Residue-free removability | no |
| • Adhesive strength | Very high adhesion | • Reusable | no |
| • Ageing resistance (UV) | yes | • Roll width max | 19 mm |
| • Applicationfield | Home, Office | • Serrated blade | _NULL |
| • Batteries included | no | • Solvent free | yes |
| • Batteries required | no | • Suitable for right and/or left handers | _NULL |
| • Ecofriendly packaging | _NULL | • Suitable surfaces | Paper, Cardboard |
| • Hand tearability | no | • Tear resistance | yes |
| • Hazard material | no | • Tensibility | 90 % |
| • Low noise unwinding | yes | • Transparency | very good |
| • Material | PP (polypropylene) | • Unwind force | 2.7 N/cm |
| • Max roll length | 33 m | • Writable | no |
| • Photocopy neutral | yes | | |

For latest information on this product please visit <http://l.tesa.com/?cp=NaN>



tesafilm[®] crystal clear

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?cp=NaN>