



[Home](#)

[Products](#)

[Support](#)

[Industries](#)

[Services](#)


[Solutions](#)

[Where to Buy](#)

[Home](#) / [Products](#) / [Fittings and Quick Couplings](#) / [Hydraulic Fittings](#) / [Crimp Fittings – No-Skive](#) / [Medium Pressure Parkrimp No-Skive Fittings - 48 Series](#) / 1XU48-16-16

Medium Pressure Parkrimp No-Skive Fittings - 48 Series

Part #: 1XU48-16-16



Parker Parkrimp Medium Pressure Fittings - 48 Series - are permanent, crimp style hydraulic fittings that allow a quick assembly with our family of Parkrimp crimpers.

[View Series Page](#) [View Catalog\(s\)](#) [Share / Email](#) [Print](#)

Technical Specifications

| | | | |
|-----------------------------|---|-----------------------|--|
| Body Material: | Steel | Industry: | Industrial Manufacturing Equipment, Off-road Machinery, Transportation |
| Product Style: | - | Port Type: | Komatsu |
| Connection 2 Type: | Female Metric - Swivel (30° Flare) | Application: | Hydraulics |
| Connection Length: | 60 mm (see drawing legend B) | Connection 2 Type: | Female, Metric, Swivel (30° Flare) |
| Maximum Operating Pressure: | 210 bar, 21.0 MPa | Hose Inside Diameter: | -16 |
| Connection 1 Size: | 25.4 mm Hose I.D., 1 inch Hose I.D., -16 (Size) | Technology: | Fluid & Gas Handling |
| Fitting Length: | n/a (see drawing legend A) | Connection 2 Size: | 1 inch |
| Brand: | Parker | Product Type: | Hose Fittings |
| Shape: | Straight | Port Type: | Komatsu |
| Hex Size 1: | n/a (see drawing legend B) | Body Material: | Steel |
| Shape: | Straight | Configuration: | Hose to Port |
| Division: | Polymer Hose Division Europe | Connection 1 Type: | Hose |
| Port Size: | 1" | For Fluid Type: | Hydraulic Fluids, Mineral Hydraulic Oil, Coolant: (Water-Glycol), Air, Water |
| | | Coating: | Chromium 6 Free-plated |

[Safety Warning](#)

Item Information