

Coupling
EAMD-67-96-32-32X32-U
Part number: 8197587



 [General operating condition](#)

Data sheet

Feature	Value
Mounting diameter 1	32 mm
Mounting diameter 2	32 mm
Size	67
Nominal length	96 mm
Mounting position	optional
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	886 kgmm ²
Transmittable torque	145 Nm
Product weight	1636 g
Note on materials	RoHS-compliant