

DREMEL® VersaFlame (2200-4)

The Dremel VersaFlame is the only stationary burner that safely combines open flame use with a catalyst and soldering head, making it the most versatile stationary burner in the market today, especially for DIY applications. The Dremel VersaFlame is powered by liquid butane gas for quick heat-up and fast recharge. Applications can be described as: soldering, shrinking, welding, etc.



PACKAGING CONTENTS

- Dremel VersaFlame
- Catalyst
- Soldering tip
- Flame extension piece
- Deflector
- Soldering tin with blue cap
- Soldering sponge + sponge box
- Inspiring welcome poster
- Instruction manual
- Tin storage case

TECHNICAL SPECIFICATIONS

Weight:	0,227 kg
Ignition:	Piëzo
Burn time :	75 min
Tank capacity:	42ml / 22g
Temperature:	1200C (open air) 680 - 1000C (hot air) 550C (tips)
Order number:	F0132200JA
EAN-Code:	8710364042081