



V200 Metal USB Flash Drive

PN: 30211 & 30212

V200 Metal USB Flash Drive is a perfect blend of performance and durability. With blazing-fast read speeds of up to 200MB/s and write speeds of 80MB/s, transferring large files has never been quicker.

Housed in a premium aluminum casing, this flash drive is built to withstand everyday wear and tear, ensuring reliability on the go.

The protective plastic cap keeps the connector safe from dust and damage, making it a rugged yet high-performance storage solution for professionals and casual users alike.

Product Details

- USB-A connection: seamless compatibility with laptops, desktops, and other devices
- High transfer speed of up to 200MB/s
- USB 3.2 Gen 1 performance
- Aluminum case: robust and lightweight design



PN: 30211 & 30212

System Requirements

- USB-A port
- Windows 11, 10, 8
- Mac OS X 14 or higher

Specifications

- Interface: USB-A / 3.2 Gen 1 backwards compatible with USB 2.0
- Power Source: USB Bus-powered

Storage and Operating Conditions

Operating Temperature: 0°C ~ +70°C

Storage Temperature: -25°C ~ +85°C

Operating Humidity: 20% ~ 65% (40°C)

Pack Contents

- Verbatim V200 USB Flash Drive

Languages

Front of pack: English

Back of pack: English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Serbian, Croatian, Traditional Chinese, Simplified Chinese, Korean, Japanese



	Read	Write
Max Data Transfer Speed	200 MB/s	80 MB/s

Reorder No.	Description	Tariff code	Barcode	EAN-128	EAN-14
30211	Verbatim V200 Metal USB Drive 64GB	85235110	023942302117	(02)00023942302117(37)10(91)802 (02)00023942302117(37)0250(91)802	20023942302111 50023942302112
30212	Verbatim V200 Metal USB Drive 128 GB	85235110	023942302124	(02)00023942302124(37)0250(91)802 (02)00023942302124(37)0250(91)802	20023942302128 50023942302129

Reorder No.	
Product Dimensions L x W x H	55.6 x 17.5 x 9.4 mm
Product Weight	8.4 g
Units per Pack	1
Pack Dimensions L x W x H	90.2 x 13 x 135 mm
Pack Weight	18.4 g
Units per Inner Carton	10
Inner Carton Dimensions L x W x H	140 x 95 x 65 mm
Inner Carton Weight	236 g
Units per Outer Carton	250
Outer Carton Dimensions L x W x H	495 x 345 x 160 mm
Outer Cartons Weight	6400 g
Outer Cartons per Layer	6
Layers per Pallet	4
Units per Pallet	6000